



3281 Guasti Road, Suite 260 Ontario, CA 91761 (909) 987-0550 (800)538-3091 Fax: (909) 987-0490

http://www.supergluecorp.com

PRODUCT DATA SHEET

Removable Thread Lock

Pacer Technology Removable Thread Lock is a medium strength anaerobic compound is used in locking, sealing, joining, and fastening of threaded metal components. Removable Thread Lock is formulated for fasteners up to $\frac{3}{4}$ " in diameter. Resistant to oil, gasoline, solvents and automotive fluids, Removable Thread Lock resists temperatures to 300° F (149° C).

PROPERTIES

<u>Liquid State</u>

<u>Chemical Base</u>

Removable Thread Lock

Anaerobic compound

Color Blue Liquid

Specific Gravity (25°F/4°C) 1.08

Flashpoint COC $^{\circ}$ F ($^{\circ}$ C) >200 (>93) Viscosity, cP 3000-9000

Typical Gap (Inches) .010
Fixture Time, minutes <25
Working Time, hours 2
Full Cure, hours 24
Corrosivity: MIL-S-22473D none

Soluble In: Acetone, MEK, Nitromethane

Cured State

Service Temperature Range -60° F to $+300^{\circ}$ F (-51 $^{\circ}$ C to $+149^{\circ}$ C)

Locking Torque*

(in-lbs) Breakaway 60-160

Prevailing 30-110
Shore D Hardness >70

Soluble In: Pacer X-8 Debonder, Acetone, Nitromethane

STORAGE AND SHELF LIFE

For optimum results, store below 90°F (32°C) in original containers. Stored under these conditions, a one-year shelf life can be expected.

^{*} Breakaway & prevailing torque tested on 3/8 zinc nuts and bolts.

Pacer Technology

Removable Thread Lock – Product Data Sheet

Page 2 of 2

APPLICATION AND CURE CHARACTERISTICS

For best results, parts should be clean and free from oil and grease, or other contaminants. Recommended surface finish is 30-80 inches. Smoother surfaces will result in lower bond strength, rougher surfaces may provide excess gap.

Fixture and cure speed is dependent upon surface activity of the metal being utilized. Steel, brass, copper, iron, and aluminum alloys containing copper will fixture faster than plated surfaces, stainless steel, and pure aluminum. Primer can be used to speed up cure. Product can be fully cured at 200° F (93° C) for 30 minutes or at 250° F (121° C) for 25 minutes.

Apply a bead around part to be bonded and assemble with a twisting motion to spread adhesive. Liquid adhesive will not center the part automatically, and additional fixture is recommended until adhesive reaches handling strength. Excess adhesive on the outside of the joint will not cure, and can be removed with a solvent-soaked cloth.

SAFETY AND HANDLING PRECAUTIONS:

Liquid adhesive can irritate skin and eyes. May cause dermatitis on prolonged contact in sensitive individuals. In case of eye contact, flush with water for 15 minutes, see a physician if symptoms persist. If swallowed, do not induce vomiting. Get immediate medical attention. Use of safety glasses, protective clothing and gloves recommended for prolonged exposure to liquid adhesive.

For more information, refer to Material Safety Data Sheet, available upon request. In case of emergency, call Pacer Technology at 800-538-3091 (outside CA only), or 909-987-0550.

PRODUCT NUMBER: N24206, N24250

2016 kr

The information in this Product Data Sheet (PDS) is of a general nature based on our knowledge and experience with this product and should be used for information and consideration purposes only. The product can have a variety of different applications, as well as differing application and working conditions in your environment that are beyond our control. Therefore, this data does not constitute a warranty, expressed or implied, statutory or otherwise, nor is it representation for which Pacer Technology assumes legal responsibility. Pacer Technology strongly recommends that users of the product independently determine the suitability of the product for their use.

Pacer Technology specifically disclaims any liability for consequential or incidental damages of any kind, including profit. Any use of this product must be determined by the user to be in accordance with applicable federal, state, provincial, and local laws and regulations.

PACER TECHNOLOGY 3281 Guasti Road, Suite 260, Ontario, CA 91761